

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



YAG-BBAR Coated Double-Convex (DCX) Lenses



Stock **#89-264-INK** [CONTACT US](#)

⊖ 1 ⊕

€60,50

ADD TO CART

Qty 1-9

€60,50

Qty 10+

€54,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 ±0.025

Back Focal Length BFL (mm):

22.47
Effective Focal Length EFL (mm): 25.00
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate: 
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 8.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.9
Radius R₁=R₂ (mm): 31.94
Clear Aperture CA (mm): 24.00
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 380 - 2500

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View