

TECHSPEC® 25mm Dia. x 30mm FL, 8-12µm Coated Germanium Meniscus Lens



Stock **#87-968** [CONTACT US](#)

⊖ 1 ⊕ **€519,00**

ADD TO CART

Qty 1-5
€519,00

Qty 6+
€415,20

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
30.00

Substrate: ☐
Germanium (Ge)

f/#:

1.2
Numerical Aperture NA: 0.42
Coating: BBAR (8000-12000nm)
Type: Meniscus Lens
Wavelength Range (nm): 8000 - 12000
Back Focal Length BFL (mm): 28.31
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Coating Specification: R _{avg} <3.0% @ 8 - 12µm
Edge Thickness ET (mm): 1.5
Focal Length Specification Wavelength (µm): 10.6
Radius R₁ (mm): 33.38
Radius R₂ (mm): 50.04
Surface Quality: 60-40
Wavelength Range (µm): 8 - 12

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant