

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm Dia. X 30mm FL, Uncoated, Hybrid Asphere



TECHSPEC® Plastic Hybrid Aspheric Lenses

Stock #65-993 CLEARANCE 3-4 DAYS

[Other Coating Options](#)



1



€84,00

ADD TO CART

Qty 1-24

€84,00

Qty 25+

€64,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Numerical Aperture NA:
0.42

Back Focal Length BFL (mm): 25.82
Substrate:  Zeonex E48R
Aspheric Design Wavelength (nm): 587.6
Coating: Uncoated
Surface Quality: 60-40
Clear Aperture CA (mm): 23.00
Edge Thickness ET (mm): 3.6
Center Thickness CT (mm): 7.30 ±0.10
f#: 1.2
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to +70
Radius R₂ (mm): 120
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 475 - 675
Conjugate Distance: Infinite

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View