

TECHSPEC® 25mm Dia. x 35mm FL, 3 - 12µm Coated, Ge Plano-Convex Lens



Stock **#87-945** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€475,00**

ADD TO CART

Qty 1-5
€475,00

Qty 6+
€380,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
35.00 @ 10.6µm

Back Focal Length BFL (mm):

34.25
Coating: BBAR (3000-12000nm)
Coating Specification: R _{avg} <5.0% @ 3 - 12μm
Substrate: □ Germanium (Ge)
Surface Quality: 60-40
Centering (arcmin): <3
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 2.25
Radius R₁ (mm): 105.14
Clear Aperture CA (mm): 24
f#: 1.4
Numerical Aperture NA: 0.36
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 3000 - 12000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
