

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

25mm Dia. x 400mm FL Uncoated, DCX N-K5 Lens



Stock #32-904 CLEARANCE 3-4 DAYS

[Other Coating Options](#)

- 1 +

€20,95

ADD TO CART

Qty 1+

€20,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
400.00 @587.6nm

Back Focal Length BFL (mm):
398.75

Coating:
Uncoated

Substrate: ☐

N-K5	
Surface Quality:	40-20
Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4
Focal Length Tolerance (%):	±1
Centering (arcmin):	<1
Center Thickness CT (mm):	5.00 ±0.10
Edge Thickness ET (mm):	4.63
Clear Aperture CA (mm):	24
f#:	16.00
Numerical Aperture NA:	0.03
Type:	Double-Convex Lens
Bevel:	Protective bevel as needed
Wavelength Range (nm):	330 - 2500

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View