

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #22-490 3-4 DAYS

[Other Coating Options](#)



1



€130,00

ADD TO CART

Qty 1-5

€130,00

Qty 6+

€104,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

45.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 37.80
Focal Length Specification Wavelength (nm): 880.00
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 13.00 ±0.20
Center Thickness CT 1 (mm): 9.00 ±0.10
Center Thickness CT 2 (mm): 4.00 ±0.10
Radius R ₁ (mm): 29.01
Radius R ₂ (mm): -25.53
Radius R ₃ (mm): -132.92
Edge Thickness ET (mm): 9.59
Substrate:  N-LAK22 / N-SF6
Surface Quality: 40-20
f/#: 1.8
Numerical Aperture NA: 0.28
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 600 - 1050

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View