

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #69-845 [CONTACT US](#)



1



€88,50

ADD TO CART

Qty 1-5

€88,50

Qty 6+

€71,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
-100.00

Substrate:
[N-BK7](#)

f/#: 4.00
Numerical Aperture NA: 0.13
Coating: VIS-NIR (400-1000nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -102.31
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 5.03
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -51.68
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant