

TECHSPEC® 25mm Dia x -50mm FL, Enhanced Aluminum, Convex Mirror



Convex Mirrors

Stock **#87-668** 3-4 DAYS

⊖ 1 ⊕ **€51,50**

ADD TO CART

Qty 1-5
€51,50
Qty 6+
€41,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-50.00

Center Thickness CT (mm):
3.00

Clear Aperture (%): 90.00
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R_{avg} >95% @ 450 - 650nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 2.22
Focal Length Tolerance (%): ±2
Radius R (mm): 100.0
Substrate: N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 450 - 650

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant