

**TECHSPEC®** 25mm Diameter x 150mm FL Uncoated, UV PCX Cylinder Lens



Stock #68-175 CLEARANCE 3-4 DAYS

⊖ 1 ⊕ **€109,95**

ADD TO CART

|         |
|---------|
| Qty 1+  |
| €109,95 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):  
150.00

Substrate: ☐  
[Fused Silica](#) (Coming 7980)

f#:  
6.00

|                                                 |
|-------------------------------------------------|
| <b>Numerical Aperture NA:</b><br>0.08           |
| <b>Coating:</b><br>Uncoated                     |
| <b>Type:</b><br>Cylinder Lens, Plano-Convex     |
| <b>Wavelength Range (nm):</b><br>200 - 2200     |
| <b>Back Focal Length BFL (mm):</b><br>147.94    |
| <b>Center Thickness CT (mm):</b><br>3.00        |
| <b>Center Thickness Tolerance (mm):</b><br>±0.1 |
| <b>Edge Thickness ET (mm):</b><br>1.85          |
| <b>Focal Length Tolerance (%):</b><br>±3        |
| <b>Radius R (mm):</b><br>68.77                  |
| <b>Surface Quality:</b><br>40-20                |
| <b>Wedge Tolerance (arcmin):</b><br>15.00       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |