

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC® Plastic Aspheric Lenses

Stock **#66-007** CLEARANCE 3-4 DAYS

[Other Coating Options](#)



1



€49,00

ADD TO CART

Qty 1-24

€49,00

Qty 25+

€35,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
20.00 @ 587.6nm

Numerical Aperture NA:
0.63

Back Focal Length BFL (mm): 14.38
Substrate:  Zeonex E48R
Aspheric Design Wavelength (nm): 587.6
Coating: Uncoated
Centering (arcmin): <5 (by design)
Surface Quality: 80-50
Clear Aperture CA (mm): 21.5
Edge Thickness ET (mm): 1.04
Center Thickness CT (mm): 9.29 ±0.20
f/#: 0.8
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to 70
Radius R₂ (mm): 103.1
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 350 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View