

TECHSPEC® 25mm Diameter x 30mm FL, Uncoated, Plastic Aspheric Lens



TECHSPEC® Plastic Aspheric Lenses

Stock **#66-009** CLEARANCE ☐ **In Stock**

[Other Coating Options](#)

-

1

+

€49,00

ADD TO CART

Qty 1-24

€49,00

Qty 25+

€35,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Numerical Aperture NA:
0.42

Back Focal Length BFL (mm): 26.04
Substrate:  Zeonex E48R
Aspheric Design Wavelength (nm): 587.6
Coating: Uncoated
Centering (arcmin): <5 (by design)
Surface Quality: 80-50
Clear Aperture CA (mm): 21.5
Edge Thickness ET (mm): 1.39
Center Thickness CT (mm): 6.54 ±0.20
f/#: 1.2
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to 70
Radius R₂ (mm): 188
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 350 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View