

TECHSPEC® 25mm Diameter x 50mm FL Uncoated, UV PCX Cylinder Lens



Stock #68-172 CLEARANCE 3-4 DAYS

⊖ 1 ⊕ **€109,95**

ADD TO CART

Qty 1+
€109,95

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm): 25.00 +0.0/-0.2
Effective Focal Length EFL (mm): 50.00
Substrate: ☐ Fused Silica (Coming 7980)
f#: 2.00

Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 200 - 2200
Back Focal Length BFL (mm): 46.58
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 1.29
Focal Length Tolerance (%): ±3
Radius R (mm): 22.93
Surface Quality: 40-20
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View