

[See all 5 Products in Family](#)

TECHSPEC® 25mm ID Side Access Mounting Plate, 60° Cutout



#85-640

Stock #85-640 [CONTACT US](#)

⊖ 1 ⊕ €59⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€59,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fixed **Function:**

Black Anodized Aluminum **Note:**

Physical & Mechanical Properties

25.0 **Plate Inner Diameter (mm):**

Bolt Circle Diameter for 6mm Dia. Thru (mm):

38.0

Bolt Circle Diameter for M3 C'bore (mm):

38.0

Dimensions (mm):

50 Dia.

Thickness (mm):

10.00

Threading & Mounting

Mounting Threads:

C'Bore Holes: (8) M3
Rod Thru Holes: (4) 6
60° cutout for side access

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 233:

[Compliant](#)

Product Details

- Specialized Plates Designed to Hold and Position Optics
- Filter Holder Plate with Interchangeable Filter Holder

These specialized TECHSPEC® Cage System Filter Holder Plates and Filter Holders are designed to hold and position a range of [optical components](#). Like a standard cage system plate, the anodized aluminum, U-shaped Filter Holder Plate features 6mm rod holes, in addition to being able to accept a Delrin® interchangeable filter holder that easily slides into the filter holder plate.

Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [Filter Holder Plate and Interchangeable Filter Holder](#).

;