

[See all 5 Products in Family](#)

**TECHSPEC® 25mm ID Side Access Mounting Plate, 60° Cutout**



#85-640

Stock **#85-640** [CONTACT US](#)

1 €59.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€59,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Black Anodized Aluminum **Note:**  
Fixed **Function:**

**Physical & Mechanical Properties**

50 Dia. **Dimensions (mm):**  
**Thickness (mm):**

10.00

Plate Inner Diameter (mm):

25.0

Bolt Circle Diameter for 6mm Dia. Thru (mm):

38.0

Bolt Circle Diameter for M3 C'bore (mm):

38.0

## Threading & Mounting

Mounting Threads:

C'Bore Holes: (8) M3  
Rod Thru Holes: (4) 6  
60° cutout for side access

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 233:

Compliant

## Product Details

- Specialized Plates Designed to Hold and Position Optics
- Filter Holder Plate with Interchangeable Filter Holder

These specialized TECHSPEC® Cage System Filter Holder Plates and Filter Holders are designed to hold and position a range of [optical components](#). Like a standard cage system plate, the anodized aluminum, U-shaped Filter Holder Plate features 6mm rod holes, in addition to being able to accept a Delrin® interchangeable filter holder that easily slides into the filter holder plate.

### Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [Filter Holder Plate and Interchangeable Filter Holder](#).