

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25mm, MgF₂ Coated, Penta Prism Beamsplitter



Stock #66-634 3-4 DAYS



1



€275,00

ADD TO CART

Qty 1-5

€275,00

Qty 6+

€220,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (°):
90, 180

Beam Deviation Tolerance (arcsec):
±10

Clear Aperture (%):
>90

Coating:

MgF ₂ on Entrance and Exit Faces
Construction: Prism
Dimensional Tolerance (mm): ±0.10
Polarization: Ts - Tp ≤ 15%
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 40-20
Type: Standard Beamsplitter
Wavelength Range (nm): 450 - 650

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View