

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Zero Series

Stock #57-594 □ In Stock



1



€103,00

ADD TO CART

Qty 1-4

€103,00

Qty 5+

€90,90

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):
12.0

Outer Diameter (mm):
25.0

Construction: Anodized Aluminum Alloy, Stainless Steel Leaves
Full Angular Range of Lever (°): 96.00
Lever Diameter (mm): 3
Lever Length (mm): 12.00
Lever Position (mm): 2.50
Number of Leaves: Two sets of 6
Operating Temperature (°C): <400
Pin Thread & Pitch: M1.4 x 0.30mm
Thickness (mm): 5.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant