

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25mm Sq., Extended Hot Mirror



Extended Hot Mirrors

Stock #46-387 3-4 DAYS



1



€66,00

ADD TO CART

Qty 1-9

€66,00

Qty 10+

€58,70

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0.00

Coating:
Hot Mirror, 0°

Substrate: BOROFLOAT®

Dimensions (mm): 25.0 x 25.0
Surface Quality: 80-50
Thickness (mm): 3.30
Thickness Tolerance (mm): ±0.2
Type: Shortpass Filter
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%): ≥85
Edges: Seamed
Coating Specification: R _{avg} ≥90% @ 750 - 1150nm R _{avg} ≥80% @ 1200 - 1600nm T _{avg} ≥85% @ 425 - 675nm
Wavelength Range (nm): 425 - 1600
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant