

[See all 11 Products in Family](#)

25mm Travel, 0.01mm Grad. Mic. Drive S-Face



Drive Mechanisms

Stock #33-731 **5 In Stock**

⊖ 1 ⊕ €102⁰⁰

ADD TO CART

Volume Pricing

Qty 1-9	€102,00 each
Qty 10-24	€91,80 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Metric **Type:**

Mitutoyo **Manufacturer:**

w/ Ratchet **Note:**

Physical & Mechanical Properties

25	Travel (mm):
0.01	Graduation (mm):
10	Stem Diameter (mm):
Plain/Spherical	Stem/Spindle:
15	Stem Length (mm):
6.35	Spindle Diameter (mm):
27	Min. Spindle Length (mm):
18	Max. Diameter (mm):
109	Overall Length (mm):

Hardware & Interface Connectivity

Metric Micrometer	Type of Drive:
-------------------	----------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential. Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

Technical Information

