

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

25mm Ultra Broadband Wire Grid Linear Polarizer



Mounted Ultra Broadband Wire Grid Linear Polarizer

Stock #34-315 [CONTACT US](#)



1



€1.325,00

ADD TO CART

Qty 1-10

€1.325,00

Qty 11+

€1.140,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
±20 without depolarization

Clear Aperture CA (mm):
19.0

Diameter (mm):
25.00

Extinction Ratio: 5000:1 @ 3200nm
Substrate: Fused Silica (Coming 7980)
Operating Temperature (°C): -40 to +200
Surface Quality: 80-50
Thickness (mm): 5.80
Transmission (%): >80 (Typical) @ 450nm
Type: Linear Polarizer
Dimensional Tolerance (mm): ±0.4
Construction: Wire Grid
Thermal Expansion: 5.5 x 10⁻⁷/°C
Alignment Tolerance (°): ±1.0
Wavelength Range (nm): 300 - 3200

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View