

TECHSPEC®

# 25mm Uncoated Ultra Precision UV Fused Silica Right Angle Prism



Stock #35-906 3-4 DAYS



1



€345,00

ADD TO CART

Qty 1-5

€345,00

Qty 6+

€310,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle Tolerance (arcsec):  
±15

Coating:  
Uncoated

Substrate: ☐  
[Fused Silica](#) (Coming 7980)

|                                                   |
|---------------------------------------------------|
| <b>Surface Quality:</b><br>20-10                  |
| <b>Type:</b><br>Right Angle Prism                 |
| <b>Dimensional Tolerance (mm):</b><br>+0.00/-0.10 |
| <b>Bevel:</b><br>Protective bevel as needed       |
| <b>Clear Aperture (%):</b><br>90                  |
| <b>Length of Hypotenuse (mm):</b><br>35.40        |
| <b>Length of Legs (mm):</b><br>25.00              |
| <b>Pyramid Tolerance (arcmin):</b><br>±1          |
| <b>Image Orientation:</b><br>Left-Handed          |
| <b>Wavelength Range (nm):</b><br>200 - 2200       |
| <b>Surface Flatness (P-V):</b><br>λ/20            |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |