

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25mm, VIS 0⁺ Coated, Rhomboid Prism



Stock #47-809 3-4 DAYS

1 €232,50

ADD TO CART

Qty 1-5

€232,50

Qty 6+

€186,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Length (mm):
25.00

Coating:
VIS 0⁺ (425-675nm)

Angle Tolerance (arcsec):
±5

Beam Deviation (arcsec): ±30
Coating Specification: R_{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): ±0.1
Image Orientation: Beam Deviation
Ray Deviation (°): 0.00
Substrate: □ N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Rhomboid Prism
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: □ Entrance/Exit Surfaces: 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View