

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #56-334 [CONTACT US](#)



1



€530,00

ADD TO CART

Qty 1-4

€530,00

Qty 5+

€468,40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (Z)

Guide System:
Slide-Fit

Type of Drive:
Metric Micrometer

Type:

Metric
Stage Size (mm): 25 x 25
Center Hole: None
Construction: Aluminium Stage
Height Adjustment (mm): ±2.5
Load Capacity (kg): 1
Mounting Threads: (7) M2 x 0.4
S.H.C.S. C'bore: (3) 2.5mm Diameters on 20mm Sq.
Straight Line Accuracy (µm): 3
Travel Per Knob Rotation (mm): 0.5
Weight (kg): 0.07

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant