

2.5" square English/Metric Adapter



Stock #55-385 **20+ In Stock**

⊖ 1 ⊕ €38²⁵

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | €38,25 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Universal **Type:**

See Figure A **Note:**

Metric **Compatible Breadboard:**

Physical & Mechanical Properties

0.5 **Thickness (inches):**

| | |
|-------------------|-------------------------|
| 2.5 | Length (inches): |
| 2.5 | Width (inches): |
| Anodized Aluminum | Construction: |

Threading & Mounting

| | |
|---|--------------------------|
| (2) 1/4-20, (2) M6 S.H.C.S Slots, (1) 1/4 and M6 S.H.C.S C'bore | Mounting Threads: |
|---|--------------------------|

Regulatory Compliance

| | |
|------------------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 250: |

Product Details

- Connects Metric/English Components to English/Metric Breadboards
- Standard 1/4-20 or M6 x 1.0 Holes and Slots
- Center C'bore Can Be Used for 1/4 or M6 S.H.C.S.
- Large and Small Sizes
- Black Anodized Aluminum Construction

Metric-English adapter plates are designed to connect our new Metric components to English breadboards while English-Metric adapter plates connect English components to Metric breadboards. These adapter plates are universal and can also be used to connect rotary stages, translation stages, and lab jacks together. See drawings for more details. For versatility, center counterbore is designed to accept both 1/4 and M6 socket head cap screws. Both are available in large 5" square or 2.5" square sizes.

Technical Information

| Type | A | B | C | D | E Mounting Thread | F Slots for S.H.C.S | Stock No. |
|----------|---------|--------|---------|--------|-------------------|---------------------|-----------|
| Figure A | 50.0mm | 25.4mm | 50.8mm | 25.0mm | M6 x 1.0 | 1/4 | #55-383 |
| Figure A | 2" | 0.984" | 1.969" | 1" | 1/4 | M6 | #55-385 |
| Figure B | 101.6mm | 25.8mm | 101.6mm | 25.0mm | M6 x 1.0 | 1/4 | #55-382 |
| Figure B | 4" | 0.969" | 3.937" | 1" | 1/4-20 | M6 | #55-384 |



