

## 2.62", English Rotary Stage



Stock #38-193 **2 In Stock**

⊖ 1 ⊕ €1.400<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€1.400,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

English **Type:**

### Physical & Mechanical Properties

1.8 **Weight (lbs):**

66.5 x 66.5 **Stage Size (mm):**

2.62 x 2.62 **Stage Size (inches):**

**Construction:**  
Aluminum top and base; steel tangent arm drive

**Center Hole:**  
0.50" Dia. Thru

**Travel (°):**  
±5 (Fine), 360 (Coarse)

**Increments (arcmin):**  
12

**Load Capacity, Normal (lbs):**  
10

**Load Capacity, Vertical (lbs):**  
4

**Type of Movement:**  
Rotary

**Guide System:**  
Ball Bearing

**Table Diameter (inches):**  
2.62

## Hardware & Interface Connectivity

**Type of Drive:**  
Tangent Arm

## Threading & Mounting

**Mounting Threads:**  
(4) 6-32 on 1.125" dia. B.C., (4) 1/4-20 on 2.00" dia. B.C.

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

## Product Details

- Low Wear, Low Friction Movement with Coarse or Fine Adjustment
- 2 or 2.62" Diameter Stages with Tapped Mounting Holes
- Calibrated Dial with 12 Minute Vernier for Accurate Read-Out

Compact miniature stages provide low-friction rotary movement with both coarse and fine adjustment. This allows for quick rotation over a continuous 360° travel, plus precise angular adjustment at any selected position. Features include preloaded angular contact ball bearing system, a positive position lock, a 2.00" or 2.62" diameter stage with tapped mounting holes and a calibrated dial with six minute vernier for accurate positional read-out. It can be combined with our compatible linear translation stages for multi-axis linear-rotary applications.

## Technical Information

