

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

266nm Flat Top Beam Shaper | πShaper 6_6_266

See More by [AdiOptica](#)



Stock #34-255 3-4 DAYS



1



€6.484,00

ADD TO CART

Qty 1-4

€6.484,00

Qty 5+

€5.835,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):

266

Diameter (mm):

39.00

Entrance Beam Diameter, 1/e² (mm):

6.3

Model Number: πShaper 6_6_266
Length (mm): 143.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <270
Wavelength Range (nm): 250 - 275
Style: Flat Top
Damage Threshold, By Design: ☐ 50 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 5.2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant