

[See all 17 Products in Family](#)

27x27mm Half Mirror Coaxial Light Blue (Recertified 05-P)

See More by [CCS](#)



Stock #21-831-RCD-05P

RECERTIFIED

1 In Stock

-

1

+

€995⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€995,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
LFV3-G-27BL	Model Number:
LED Illuminator	Type of Illumination:
CCS	Manufacturer:
Coaxial Light	Geometry:

Illumination Mode:	
Constant	
Physical & Mechanical Properties	
Dimensions (mm):	
W 39 mm x D 56 mm x H 31 mm	
Weight (g):	
110	
Active Area (mm):	
27.4 mm x 27 mm	
Optical Properties	
Color:	
Blue	
Wavelength (nm):	
470	
Electrical	
Power Consumption (W):	
5	
Hardware & Interface Connectivity	
Input Voltage (V):	
24	
Power Supply:	
Power Supply Required and Sold Separately.	
USA: #73-491	
Europe: #73-491	
Japan: #89-513	
Korea: #33-773	
China: #73-491	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- Unique Design Prevents Ghost Images
- Available in Red, White, and Blue
- Ideal for Use with High Resolution Cameras

CCS High-Resolution Coaxial Lights are designed to provide diffused lighting for high-resolution imaging of shiny, flat surfaces. Designed to prevent ghost reflections and achieve higher system resolution, these coaxial lights integrate a unique thin beamsplitter to minimize deviation through in the imaging path. CCS High-Resolution Coaxial Lights are ideal for industrial imaging applications including inspection of glossy surfaces, pattern detection on PCBs, and measuring dimensions of glass.

Technical Information

