

2m 4-pin M12 Cable



Stock #74-248 NEW **1 In Stock**

⊖ 1 ⊕ €45⁰⁰

ADD TO CART

Volume Pricing

Qty 1+ €45,00 each

Need More? [Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Advanced Illumination **Manufacturer:**

Hardware & Interface Connectivity

4-pin Female M12, Flying Leads **Connector:**

2 **Length of Cable (m):**

Regulatory Compliance

Product Details

- IP67 For Dust and Debris Protection
- High Intensity Illumination Profile
- Available in UV, White, Blue, Green, Red, & NIR
- Ideal For Line Scan Applications

The Advanced Illumination Sealed High Intensity Line Lights provide a uniform illumination profile for line scan applications in rugged environments. These lights are IP67-rated for protection against dust, debris, and liquid, offering reliable performance in harsh environments. The lights are available in UV, white, blue, green, red, and NIR wavelengths and are passively cooled for continuous long-term operation. The Advanced Illumination High Intensity Line Lights feature an embedded controller that is designed for continuous operation and housed within the light itself. These lights are ideal for rugged line scan applications including inspection of sheetrock, lumber, and ceramics, and food and beverage washdown environments.
