

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 3" Diameter X 17.5" FL Protected Aluminum, Parabolic Mirror



Stock #32-064-522 ☐ In Stock



1



€393,00

ADD TO CART

Qty 1-9

€393,00

Qty 10+

€334,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±1

Surface Quality: 60-40

Surface Accuracy:

N/8
Diameter (inches): 3.0 +0.04/-0
Diameter (mm): 76.20 +1.0/-0
Effective Focal Length EFL (inches): 17.5
Effective Focal Length EFL (mm): 444.50
Radius of Curvature (mm): 889.00
Aperture (f/#): f/5.8
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 69
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Type: Parabolic Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant