

[All Products](#) / [Optics](#) / [Diffraction Gratings](#) / [Richardson Gratings™ High Precision](#)

[See all 37 Products in Family](#)


Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Grating

See More by [Richardson Gratings™](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Grating

Stock #15-773 **20+ In Stock**

1

€195^{,00}

ADD TO CART

Volume Pricing	
Qty 1-9	€195,00 each
Qty 10-24	€175,50 each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
Spec Sheets:pdf	
eDrawing:eprt	Whitepapers
EO Spec Sheet	Download All

Prices shown are exclusive of VAT/local taxes

General

Type: Reflective Diffraction Grating

Master Reference: 1156

Physical & Mechanical Properties

Dimensions (mm): 25.0 x 25.0 ±0.1

Clear Aperture (%): >90

Construction: Ruled Grating

Length (mm): 25.00

Thickness (mm): 6.00 ±0.5

Width (mm): 25.00

Centering of Ruled Area on Substrate (mm): ±1

Alignment of Grooves to Edge (°): ±0.15

Groove Spacing Tolerance (%): <0.05

Optical Properties

Groove Density (grooves/mm): 300

Wavelength Range (nm): 1000 - 5000

Blaze Wavelength (nm): 3000 ±25

Blaze Angle (°): 26.7

Peak Efficiency, Typical (%): 72 (2nd order)

Coating: Aluminium

Substrate: Float Glass

Reflected Wavefront, RMS: λ/4

Polarization: S and P

Spectral Order (m): 1

Regulatory Compliance

Certificate of Conformance: [View](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Excellent Efficiency at Blaze Wavelength and Blaze Angle
- Superior Dimensional Tolerances
- Ideally Suited for Spectroscopic Applications
- Custom Sizes Available


Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings are designed for consistent, predictable performance. The gratings are manufactured from highly accurate masters to provide a high level of repeatability to simplify OEM system designs by reducing the need for tedious alignment adjustments. With $\lambda/4$ reflected wavefronts and up to 90% diffraction efficiency, these gratings are specified to meet the needs of the most demanding applications such as high-resolution spectroscopy. Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings feature bare aluminum coatings, allowing for options that range from 250 to 10,000nm with excellent peak efficiencies. Custom sizes available on request.

Note: The surface of these gratings is very sensitive and should never be touched when handling the optic. If cleaning is required to remove dust particles, non-contact cleaning using clean compressed air is recommended.

Technical Information


Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools


Related Products



Richardson Gratings™ Echelle Reflective Diffraction Gratings



Diffraction Gratings



Diffraction Gratings



Adjustable Grating Mounts

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.
Select Your Country/Region:

Frequently Purchased Together



#15-770 - Richardson Gratings™ 75 Grooves, 25 x 25mm, 10µm, Plane Ruled Reflection Grating
€195,00

Qty




#25-836 - 10mm Square Microlens Array Mount, 2.25mm Thick
€82,00

Qty

Resources


Media Type

- Application Note
- Video
- FAQ
- Glossary



WEBINARS

Helpful Tips for Selecting the Correct Diffraction Grating




APPLICATION NOTE

All About Diffraction Gratings




VIDEO

Richardson Gratings™ Unboxing



FAQ

What is the difference between holographic...



FAQ

How do the efficiency curves relate to the actual...



FAQ

What is the difference between Rowland circl...

[View More](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: