

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

225mm Max. Aperture, Iris Diapnragm



Stock #70-895 3-4 DAYS

-

1

+

 €772,00

ADD TO CART

Qty 1-4

€772,00

Qty 5+

€682,40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
12.0

Maximum Aperture (mm):
225.0

Outer Diameter (mm):

300.0
Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 5.00
Lever Length (mm): 40.50
Number of Leaves: 18.00
Thickness (mm): 19.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)