

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

300µm Aperture Diameter, 12.7 mm Mounted, Acktar Blackened Pinhole

See More by Acktar



Acktar Blackened Pinholes (mounted)



Stock #16-827 3-4 DAYS



1



€144,00

ADD TO CART

Qty 1-9

€144,00

Qty 10+

€129,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Mounted

Outer Diameter (mm): 12.7 ±0.2
Construction: Stainless Steel
Fixed Aperture Diameter (µm): 300 ±3
Diameter of Mount (mm): 12.7 ±0.2
Thickness (mm): 0.02 nominal
Coating: Magic Black™
Mount Thickness (mm): 2.0 ±0.1
Absorbance (%): 99
Model Number: PA-1-2-300-05

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant