

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

304.8mm High Resolution Image Conduit with 24µm Fibers



Stock #38-304 3-4 DAYS



1



€622,00

ADD TO CART

Qty 1-4

€622,00

Qty 5+

€547,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Minimum Bend Radius (mm):
25.6

Diameter Tolerance (inches):
±0.010

Length (mm):
304.80

Numerical Aperture NA:

0.55
Number of Fibers: 50419.00
Operating Temperature (°C): 454.00
Outer Diameter (mm): 6.40
Resolution: 20 lp/mm
Transformation Temperature (°C): 704.00
Transmission (%): 35 - 45
Fiber Diameter (µm): 24.00
Type: High-Resolution
Length Tolerance (inches): ±0.030
Packing Fraction (%): 100.00
Index of Refraction n_d - Core: 1.58
Index of Refraction n_d - Cladding: 1.48
Wavelength Range (nm): 350 - 1500

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View