

[See all 10 Products in Family](#)

## TECHSPEC® 30mm - 50mm Length, C-Mount Fine Focus Tube



Stock #03-625 **20+ In Stock**

- 1 + €118<sup>.00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	€118,00 each
Qty 5-9	€104,40 each
Qty 10-25	€96,40 each
Need More?	<a href="#">Request Quote</a>

! Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Fine Focus Tube **Type:**

Extension Tube (Adjustable) **Function:**

### Physical & Mechanical Properties

30.0 - 50.0 **Extension Length (mm):**

18.0	Clear Aperture CA (mm):
30.0	Outer Diameter (mm):
18.0	Inner Diameter (mm):

## Threading & Mounting

C-Mount	Thread Type:
M18 x 0.5	Barrel Thread:

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 235:

## Product Details

- Finely Threaded Internal Barrel for Fine Focus Adjustments
- Inner Diameter Baffle Thread for Stray Light Reduction
- Knurled Lip on Female End for Controlled Adjustments

TECHSPEC® C, S, and T-Mount Fine Thread Focus Tubes are used for making precision adjustments to optical element positions within a system. These tubes feature an outer barrel with male C, S, or T-Mount thread at the base end and a finely threaded interior barrel to allow for fine focusing. The secondary barrel has a female S, C, or T-Mount thread, knurled ring at the front end for easy adjustment, and a threaded interior for light baffle. Set screws can be used to fix the extension position. TECHSPEC C, S, and T-Mount Fine Thread Focus Tubes offer different extension length options to meet specific application demands.

**Note:** Compatible Allen wrenches for C, S, and T-Mount Fine Thread Focus Tubes ([#56-271](#), [#55-452](#), and [#58-637](#), respectively) sold separately.

## Technical Information

