

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #67-260 3-4 DAYS

[Other Coating Options](#)



1



€480,00

ADD TO CART

Qty 1-5

€480,00

Qty 6+

€384,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.1

Effective Focal Length EFL (mm):
17.50 @ 587.6nm

Numerical Aperture NA:

0.86
Back Focal Length BFL (mm): 9.43
Substrate: ☐ N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (600-1050nm)
Coating Specification: R _{avg} ≤1.5% @ 600 - 1050nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 27
Edge Thickness ET (mm): 1.78
Center Thickness CT (mm): 13.50 ±0.1
f/#: 0.58
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Power (diopters): 57.14

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant