

30mm Dia. 405nm λ/4 Quartz Waveplate Multiple Order



Stock **#83-925** CLEARANCE 3-4 DAYS

- 1 +

€252,95

ADD TO CART

Qty 1+
€252,95

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm): 23.0
Coating: Laser V-Coat (405nm)
Design Wavelength DWL (nm): 405
Diameter (mm): 30.00 +0.00/-0.25
Substrate: ☐ Crystal Quartz

Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 6.00 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/8 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0015
Retardance Order: Multiple Order

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View