

**TECHSPEC®** 30mm Dia., Enhanced Deep UV (DUV) Mirror



Precision Ultraviolet Mirrors

Stock **#18-745** 3-4 DAYS



1



€310,00

ADD TO CART

Qty 1-5

€310,00

Qty 6+

€248,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
30.00 +0.0/-0.2

**Surface Flatness (P-V):**  
λ/10

**Substrate:** ☐

|                                                                                                             |
|-------------------------------------------------------------------------------------------------------------|
| <a href="#">Fused Silica</a> (Coming 7980)                                                                  |
| <b>Back Surface:</b><br>Commercial Polish                                                                   |
| <b>Surface Quality:</b><br>10-5                                                                             |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≥92% @ 190 - 250nm<br>R <sub>avg</sub> ≥83% @ 250 - 900nm |
| <b>Coating:</b><br>Enhanced Aluminum (190-900nm)                                                            |
| <b>Coating Type:</b><br>Metal                                                                               |
| <b>Angle of Incidence (°):</b><br>0                                                                         |
| <b>Clear Aperture (%):</b><br>90                                                                            |
| <b>Design Wavelength DWL (nm):</b><br>190                                                                   |
| <b>Parallelism (arcsec):</b><br><30                                                                         |
| <b>Thickness (mm):</b><br>5.00 ±0.20                                                                        |
| <b>Type:</b><br>Flat Mirror                                                                                 |
| <b>Wavelength Range (nm):</b><br>190 - 900                                                                  |
| <b>Vacuum Compatibility:</b><br>10 <sup>-7</sup> Torr                                                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |