

TECHSPEC 30mm ID Fixed Angle Mounting Plate



30mm ID Fixed Angle Mounting Plate, #85-622

Stock **#85-622** **2 In Stock**

⊖ 1 ⊕ €57⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€57,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Angle Adjustment **Function:**

Physical & Mechanical Properties

30.0 **Plate Inner Diameter (mm):**

38.0 **Bolt Circle Diameter for M3 C'bore (mm):**

Construction:

Black Anodized Aluminum

50 Dia. **Dimensions (mm):**

10.00 **Thickness (mm):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **REACH 241:**

Product Details

- Multiple Angular Positioning Options
- Fixed and Continuous Adjustment Plates Available
- Anodized Aluminum Construction

TECHSPEC® Cage System Angle Adjustment Plates attach to [standard mounting plates](#) via angle brackets, and offer a range of angular positioning options. The fixed angle mounting plates feature M3 C-Bore holes positioned at 30° increments to introduce 30°, 60°, or 90° bends in the optical path. Swivel adapter plates are designed to be used in pairs, and enable continuous angle adjustment. [#85-692](#) or [#85-701](#) post adapter for 25mm plates serves as a joint between two swivel adapter plates. Suspending a tilt plate between two standard cage system plates allows an optic or mount to be tilted with respect to the optical axis.

Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [How to Build a Swivel Joint Assembly](#).