

## 30µm Aperture Diameter, Mounted, Precision Pinhole



30µm Aperture Diameter, Mounted, Precision Pinhole, #84-065

Stock **#84-065** 3-4 DAYS



1



€75,00

ADD TO CART

Qty 1-5

€75,00

Qty 6+

€66,20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:  
Mounted

Outer Diameter (mm):  
25 +0.4/-0.000

Construction:  
Stainless Steel

|                                     |
|-------------------------------------|
| Fixed Aperture Diameter (μm):<br>30 |
| Thickness (mm):<br>0.03 Nominal     |
| Aperture Tolerance (μm):<br>±5      |
| Mount Thickness (mm):<br>1.25 ±0.05 |
| Aperture Centration (μm):<br>±125   |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |
| Reach 235:<br><a href="#">Compliant</a>             |