

3.0X InfiniFlex HD Compact Lens

See More by [Infinity Photo-Optical Company](#)



Stock **#89-950** **1 In Stock**

-

1

+

€975^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€975,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fixed Magnification Lens

Type:

Physical & Mechanical Properties

78.00

Length (mm):

15.0

Maximum Diameter (mm):

Optical Properties

Horizontal Field of View, 1/2" Sensor:	
2.1mm	
Numerical Aperture NA:	
0.13	
Primary Magnification PMAG:	
3X	
Working Distance (mm):	
20.00	
Sensor	
Maximum Sensor Format:	
2/3"	
Threading & Mounting	
Mount:	
C-Mount	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Reach 224:	
Compliant	
Certificate of Conformance:	
View	

Product Details

- Multiple Options Available by Combining Main Bodies and Amplifiers
- High Light Throughput and Resolution with 0.13 NA
- Standardized 20mm Working Distance

InfiniFlex™ HD Compact Lenses are high performance micro imaging lenses designed to maximize system resolution. These lenses support up to 2/3" format sensors and feature an easy-to-use, patent-pending design. Simply choose a main body and an optional amplifier to reach magnifications ranging from 2X to 12X. The 2X PLAN version is designed specifically for increased full field imaging. For applications requiring brightfield or darkfield illumination, a 21mm Ring Light Adapter is available and allows a ring light to be moved along the body of the 15mm diameter lens to permit full angular illumination. A retainer is also available for integrating a 20mm filter in between the lens and the camera. Because the InfiniFlex™ HD Compact Lenses share similar dimensions as the [InfiniStix™ Imaging Lenses](#), the two lenses can be used together to achieve high resolutions and increased depth of field.

Technical Information

