

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Protected Gold Off-Axis Ellipsoidal Mirror

Stock #12-498 3-4 DAYS



1



€335,00

ADD TO CART

Qty 1-5

€335,00

Qty 6+

€301,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Magnification:

2.5X

Substrate:

Aluminum 6061-T6

Surface Quality:

60-40

Surface Roughness (Angstroms): <100 RMS
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Dimensions (mm): 31.75 x31.75
Off-Set Angle (°): 65.44
Type: Off-Axis Ellipsoidal Mirror
Wavelength Range (nm): 700 - 10000
Y Offset (mm): 49.38
Image Distance (mm): 83.82
Object Distance (mm): 33.02

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View