

32mm Dia. x -200mm FL, Grade 2, Double-Concave Lens



Stock **#53-113** CLEARANCE **20+ In Stock**

-

1

+

€11^{.25}

ADD TO CART

Volume Pricing	
Qty 1+	€11,25 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Double-Concave Lens

Physical & Mechanical Properties

Diameter (mm):

32.00

Optical Properties

Effective Focal Length EFL (mm):

-200.00

6.25	f##:
0.08	Numerical Aperture NA:
Material Properties	
Grade 2	Grade:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Ideal for Experimenting and Prototyping Applications
 - Quantities Extremely Limited, Buy While Supplies Last
 - For Even More Deals, Check out [Mega Clearance: Optics](#)
- Double-concave (DCV) lenses have two inward curved surfaces and a negative focal length. They are used for image reduction and to spread light.

Experimental Quality Double-Concave (DCV) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

