

334nm CWL, 10nm FWHM, 25mm Mounted Diameter



Stock **#65-672** CLEARANCE 3-4 DAYS

⊖ 1 ⊕

€134,95

ADD TO CART

Qty 1+
€134,95

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm): 25.00 +0.0/-0.2
Angle of Incidence (°): 0
Optical Density OD (Average): ≥3.0
Clear Aperture CA (mm): 21.0

Center Wavelength CWL (nm): 334.00 ±2
Center Wavelength CWL Tolerance (nm): ±2
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): ≥25
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: Mercury Emission
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 7.5 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View