

## 34mm Diameter, Prism Mount Metric



Stock #55-012 **20+ In Stock**

- 1 + €421<sup>.00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€421,00 each
Qty 5-25	€378,90 each
Qty 26-49	€358,10 each
Need More?	<a href="#">Request Quote</a>

! Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Adjustable - Rotary & Tip-Tilt **Type:**

Cube/Prism **Type of Optics:**

### Physical & Mechanical Properties

±3 **Fine Rotation (°):**

Fine Tilt Angle (°):  
±3

## Threading & Mounting

Size of Compatible Optics (mm):  
20.0

Compatible Post:  
M6 x 1.0

## Regulatory Compliance

RoHS 2015:  
[Exempt](#)

Certificate of Conformance:  
[View](#)

Reach 247:  
[Contains SVHC\(s\)](#)

## Product Details

- Precision Fine Movement
- Holds Prisms up to 30mm
- Black Anodized Aluminum
- [Posts](#) and [Post Holders](#) Required for Mounting

Metric Prism Mounts permit ±3° precision fine movement rotation and ±3° X-Y axes tilt control. These mounts feature durable black anodized aluminum construction and hold prisms up to 30mm. [Posts](#) and [post holders](#) are required for mounting to a breadboard.

## Technical Information

Mount Diameter A	Maximum Prism Size B	Base Height C	Maximum Total Mount Height D	Stock No.
34	20	30	76	<a href="#">#55-012</a>
50	30	45	102	<a href="#">#55-013</a>

