

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

34mm Diameter, UV Cut-Off Filter



Stock #54-049 CLEARANCE 3-4 DAYS

-

1

+

 €14,95

ADD TO CART

Qty 1+

€14,95

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
34.00 +0.0/-0.2

Cut-On Wavelength (nm):
390.00

Glass/Filter Number:
L-39

Substrate: 
Hoya L-39

Operating Temperature (°C):
-15 to 70

Coating: AR Coating
Color: Clear, Green Tint
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): >80 (avg)
Type: UV Cut-Off Filter
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View