

TECHSPEC® 35mm 488nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#48-877** CLEARANCE 3-4 DAYS



1



€249,95

ADD TO CART

Qty 1+

€249,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Clear Aperture (%):
90.00

Coating Specification:
R_{abs} <0.25% @ 488nm

Construction:

Cube
Design Wavelength DWL (nm): 488
Dimensions (mm): 35.0 x 35.0 x 35.0 ±0.1
Extinction Ratio: 1000:1
P-Polarization Transmission (%): >95
S-Polarization Reflection (%): >99.5
Substrate:  N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 40-20
Type: Linear Polarizer

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View