

## 35mm Dia. x 15mm FL Protected Aluminum, Concave Mirror



Stock **#43-467** ☐ In Stock

1  **€50,50**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-49                      |
| €50,50                        |
| Qty 50+                       |
| €43,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐  
[N-BK7](#)

Focal Length Tolerance (%):  
±2

Surface Quality:  
80-50

Diameter (mm):

|                                                                                                            |
|------------------------------------------------------------------------------------------------------------|
| 35.00 ±0.50                                                                                                |
| <b>Effective Focal Length EFL (mm):</b><br>15.00                                                           |
| <b>Radius of Curvature (mm):</b><br>30.00                                                                  |
| <b>Aperture (f/#):</b><br>f/0.43                                                                           |
| <b>Coating:</b><br>Protected Aluminum (400-2000nm)                                                         |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >85% @400 - 700nm<br>R <sub>avg</sub> >90% @400 - 2000nm |
| <b>Coating Type:</b><br>Metal                                                                              |
| <b>Clear Aperture (%):</b><br>90                                                                           |
| <b>Edge Thickness ET (mm):</b><br>6.0                                                                      |
| <b>Radius R<sub>1</sub> (mm):</b><br>30.00                                                                 |
| <b>Thickness Tolerance (mm):</b><br>±0.5                                                                   |
| <b>Type:</b><br>Spherical Mirror                                                                           |
| <b>Wavelength Range (nm):</b><br>400 - 2000                                                                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |