

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



3.5mm Focal Length



Stock #15-612 3-4 DAYS



1



€485,00

ADD TO CART

Qty 1+

€485,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Fixed

Length (mm):
41.96

Horizontal Field of View, 1/2" Sensor:
94.13°

Filter Thread:

M62 x 0.75 (Female)
Maximum Diameter (mm): 65.00
Horizontal Field of View, 1/3" Sensor: 74.44°
Maximum Rear Protrusion (mm): 2.7
Maximum Image Circle (mm): 9.00
Numerical Aperture NA, Object Side: 0.013
Number of Elements (Groups): 10 (9)
Note: C-Mount compatible with O-ring 25mm ID x 2mm
Horizontal Field of View, 1/1.8" Sensor: 102.34°
Horizontal Field of View, 1/2.5" Sensor: 86.75°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 3.50
Primary Magnification PMAG: 0.303
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 75 - ∞
Mount: C-Mount
Aperture (f/#): f/11
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 34.70
Object Space Principal Plane (mm): -22.37
Image Space Principal Plane (mm): 32.70
Field of View at Max Sensor Format: Horizontal: 102.34° Vertical: 82.28° Diagonal: 116.98°
Maximum Distortion (%): 21.12
Exit Pupil Position (mm): -15.89
Environmental Rating: IPX7
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View