

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



35mm Focal Length Lens, 1" Sensor Format, #63-247

Stock **#63-247** 3-4 DAYS

[Similar Products](#)



1



€700,00

ADD TO CART

Qty 1+

€700,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:

Variable

Length (mm):

43.00

Filter Thread:

M35.5 x0.50

Maximum Diameter (mm):

42.0

Weight (g): 130
Horizontal Field of View, 1" Sensor: 20.9°
Maximum Image Circle (mm): 16.00
TV Distortion (%): <0.5
Type: Fixed Focal Length Lens
Focal Length FL (mm): 35.00
Maximum Sensor Format: 1"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Maximum Distortion (%): < -0.05%
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)