

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

3600 Grooves/mm, 25mm Square, UV Holographic Grating



Reflective Holographic Gratings

Stock #43-228 3-4 DAYS



1



€166,00

ADD TO CART

Qty 1+

€166,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
3600

Wavelength Range (nm):
250 - 400

Dimensions (mm):
25.0 x 25.0 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 25.00
Substrate: ☐ Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Wavelength: UV
Width (mm): 25.00
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 56
Peak Efficiency Avg, Typical (%): >39

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
