

36" Length, Dovetail Optical Rail



36" Length, Dovetail Optical Rail, #54-402

Stock **#54-402** 3-4 DAYS



1



€322,00

ADD TO CART

Qty 1-4

€322,00

Qty 5+

€300,40

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Dovetail

Type of Drive:
Manual

Type: Universal (Metric & English)
Travel (mm): 914.4
Travel (inches): 36
Length (inches): 36
Length (mm): 914.40
Construction: Black Anodized Aluminum
Mounting Threads: C'bore Holes and Slots only for 1/4" (or M6) S.H.C.S
Note: Rail

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
